

SIO-MB16ND3 Cut Sheet



STRIDE discrete input module, 16-point, 12-24 VDC, sinking/sourcing, 2 isolated common(s), 8 point(s) per common, (1) Ethernet (RJ45) port(s), Modbus TCP Server.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SIO-MB16ND3>

Technical Specifications

Brand	STRIDE
Item	Input module
I/O Module Type	Discrete
Number of Input Points	16
Nominal Input Voltage	12-24 VDC
Discrete Input Type	Sinking/sourcing
Number of Isolated Input Commons	2
Number of Points per Common	8
Communication Port and Connection Type(s)	(1) Ethernet (RJ45)
Port Protocol(s)	Modbus TCP Server
Port Speed(s)	10/100 Mbps
External Power Requirement	10-30 VDC
Programming Software	None, configure via Internet browser

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document