

SJC-100C-47.625 Cut Sheet



Sung-II Machinery drive coupling hub, jaw type, aluminum alloy, clamp, size 100, 1-7/8in bore. Requires SJC-100 series spiders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJC-100C-47.625>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Jaw type
Material	Aluminum alloy
Slip Torque	480 N·m
Maximum Angular Misalignment	1.0 degrees
Maximum RPM	3500
Attachment Style	Clamp

Coupling Size	100
Overall Length	140.2mm
Bore Diameter	1-7/8in
Outside Diameter	104mm
Clamp Screw Fastening Torque	90 N·m
Clamp Screw Size	M12-1.75 x 40mm
Requires	SJC-100 series spiders

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SJC-100C-47.625.pdf>
See store item page for other formats.