

SJC-20C-4.76 Cut Sheet



Sung-II Machinery drive coupling hub, jaw type, aluminum alloy, clamp, size 20, 3/16in bore. Requires SJC-20 series spiders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJC-20C-4.76>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Jaw type
Material	Aluminum alloy
Slip Torque	1.5 N·m
Maximum Angular Misalignment	1.0 degrees
Maximum RPM	15000
Attachment Style	Clamp

Coupling Size	20
Overall Length	30mm
Bore Diameter	3/16in
Outside Diameter	20mm
Clamp Screw Fastening Torque	1 N·m
Clamp Screw Size	M2.6-0.45 x 10mm
Requires	SJC-20 series spiders

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SJC-20C-4.76.pdf>
See store item page for other formats.