

SJC-55C-25.4 Cut Sheet



Sung-II Machinery drive coupling hub, jaw type, aluminum alloy, clamp, size 55, 1in bore. Requires SJC-55 series spiders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJC-55C-25.4>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Jaw type
Material	Aluminum alloy
Maximum Angular Misalignment	1.0 degrees
Maximum RPM	6500
Attachment Style	Clamp
Coupling Size	55
Bore Diameter	1in
Outside Diameter	55mm
Clamp Screw Fastening Torque	13N-m
Clamp Screw Size	M6
Requires	SJC-55 series spiders

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement