

SJC-65C-19.05 Cut Sheet



Sung-II Machinery drive coupling hub, jaw type, aluminum alloy, clamp, size 65, 3/4in bore. Requires SJC-65 series spiders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJC-65C-19.05>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Jaw type
Material	Aluminum alloy
Maximum Angular Misalignment	1.0 degrees
Maximum RPM	5500
Attachment Style	Clamp
Coupling Size	65
Bore Diameter	3/4in
Outside Diameter	65mm
Clamp Screw Fastening Torque	30N-m
Clamp Screw Size	M8
Requires	SJC-65 series spiders

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement