

SJCA-30C-10 Cut Sheet



Sung-II Machinery drive coupling hub, jaw type, aluminum alloy, clamp, size 30, 10mm bore. Requires SJC-30 series spiders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJCA-30C-10>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Sung-II Machinery |
| Item | Drive coupling hub |
| Coupling Type | Jaw type |
| Material | Aluminum alloy |
| Maximum Angular Misalignment | 1.0 degrees |
| Maximum RPM | 10000 |
| Attachment Style | Clamp |
| Coupling Size | 30 |
| Bore Diameter | 10mm |
| Outside Diameter | 30mm |
| Clamp Screw Fastening Torque | 3.5N-m |
| Clamp Screw Size | M4 |
| Requires | SJC-30 series spiders |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |