

SJEOOW-14-2BK-1 Cut Sheet



Southwire portable cord, unshielded, SJEOOW, 300V, 2 conductors, 14 AWG, TPE conductor insulation material, black and white, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJEOOW-14-2BK-1>

Technical Specifications

Brand	Southwire
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SJEOOW
Applicable Standards	UL 62
Application	General purpose
Flexibility	Flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	14 AWG
Conductor Stranding	41-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE
Conductor Insulation Color	Black and white

Shielding	Unshielded
Jacket Material	TPE
Jacket Color	Black
Nominal Overall Cable Diameter	0.345in
Bulk Length	Cut to length
Package Type	1 to 75ft = Coil, 76 to 320ft = 14 x 7in Reel, 321 to 470ft = 14 x 10in Reel, 471 to 720ft = 16 x 10in Reel, 721 to 1020ft = 18 x 10in Reel, 1021 to 1330ft = 18 x 13in Reel, 1331 to 2860ft = 24 x 17in Wooden Reel, 2861 to 4700ft = 30 x 17in Wooden Reel, 4701 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement