

SJEOOW-14-3BK-1 Cut Sheet



Southwire portable cord, unshielded, SJEOOW, 300V, 3 conductors (includes ground), 14 AWG, TPE conductor insulation material, black, white and green, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJEOOW-14-3BK-1>

Technical Specifications

Brand	Southwire	Shielding	Unshielded
Item	Cord	Jacket Material	TPE
Wire/Cable Type	Portable	Jacket Color	Black
UL Wire/Cable Type	SJEOOW	Nominal Overall Cable Diameter	0.37in
Applicable Standards	UL 62	Bulk Length	Cut to length
Application	General purpose	Package Type	<ul style="list-style-type: none">• 20 to 75ft = Coil• 76 to 285ft = 14 x 7in Reel• 286 to 405ft = 14 x 10in Reel• 406 to 625ft = 16 x 10in Reel• 626 to 870ft = 18 x 10in Reel• 871 to 1135ft = 18 x 13in Reel• 1136 to 2535ft = 24 x 17in Wooden Reel• 2536 to 4060ft = 30 x 17in Wooden Reel• 4061 to 5000ft = Large Wooden Reel
Flexibility	Flexible		
Voltage Rating	300V		
Conductors	3 conductors (includes ground)		
Conductor Size	14 AWG		
Conductor Stranding	41-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	TPE		
Conductor Insulation Color	Black, white and green		

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement