

# SJEOOW-14-3BK-1 Cut Sheet



Southwire portable cord, unshielded, SJEOOW, 300V, 3 conductors (includes ground), 14 AWG, TPE conductor insulation material, black, white and green, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJEOOW-14-3BK-1>

## Technical Specifications

<b>Brand</b>	Southwire
<b>Item</b>	Cord
<b>Wire/Cable Type</b>	Portable
<b>UL Wire/Cable Type</b>	SJEOOW
<b>Applicable Standards</b>	UL 62
<b>Application</b>	General purpose
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	3 conductors (includes ground)
<b>Conductor Size</b>	14 AWG
<b>Conductor Stranding</b>	41-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	TPE
<b>Conductor Insulation Color</b>	Black, white and green

<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	TPE
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.37in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 75ft = Coil, 76 to 280ft = 14 x 7in Reel, 281 to 400ft = 14 x 10in Reel, 401 to 630ft = 16 x 10in Reel, 631 to 890ft = 18 x 10in Reel, 891 to 1150ft = 18 x 13in Reel, 1151 to 2480ft = 24 x 17in Wooden Reel, 2481 to 4090ft = 30 x 17in Wooden Reel, 4091 to MAX = Large Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	E46194
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	90458
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>