

SJEOOW-16-2BK-1 Cut Sheet



Southwire portable cord, unshielded, SJEOOW, 300V, 2 conductors, 16 AWG, TPE conductor insulation material, black and white, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJEOOW-16-2BK-1>

Technical Specifications

Brand	Southwire	Shielding	Unshielded
Item	Cord	Jacket Material	TPE
Wire/Cable Type	Portable	Jacket Color	Black
UL Wire/Cable Type	SJEOOW	Nominal Overall Cable Diameter	0.315in
Applicable Standards	UL 62	Bulk Length	Cut to length
Application	General purpose	Package Type	1 to 75ft = Coil, 76 to 390ft = 14 x 7in Reel, 391 to 560ft = 14 x 10in Reel, 561 to 870ft = 16 x 10in Reel, 871 to 1230ft = 18 x 10in Reel, 1231 to 1590ft = 18 x 13in Reel, 1591 to 3430ft = 24 x 17in Wooden Reel, 3431 to 5640ft = 30 x 17in Wooden Reel, 5641 to MAX = Large Wooden Reel
Flexibility	Flexible		
Voltage Rating	300V		
Conductors	2 conductors		
Conductor Size	16 AWG		
Conductor Stranding	26-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	TPE		
Conductor Insulation Color	Black and white		

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement