

# SJEOOW-18-2BK-1 Cut Sheet



Southwire portable cord, unshielded, SJEOOW, 300V, 2 conductors, 18 AWG, TPE conductor insulation material, black and white, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJEOOW-18-2BK-1>

## Technical Specifications

<b>Brand</b>	Southwire	<b>Shielding</b>	Unshielded
<b>Item</b>	Cord	<b>Jacket Material</b>	TPE
<b>Wire/Cable Type</b>	Portable	<b>Jacket Color</b>	Black
<b>UL Wire/Cable Type</b>	SJEOOW	<b>Nominal Overall Cable Diameter</b>	0.29in
<b>Applicable Standards</b>	UL 62	<b>Bulk Length</b>	Cut to length
<b>Application</b>	General purpose	<b>Package Type</b>	1 to 50ft = Coil, 51 to 99ft = Coil, 100 to 460ft = 14 x 7in Reel, 461 to 660ft = 14 x 10in Reel, 661 to 1030ft = 16 x 10in Reel, 1031 to 1450ft = 18 x 10in Reel, 1451 to 1880ft = 18 x 13in Reel, 1881 to 4050ft = 24 x 17in Wooden Reel, 4051 to 6660ft = 30 x 17in Wooden Reel
<b>Flexibility</b>	Flexible		
<b>Voltage Rating</b>	300V		
<b>Conductors</b>	2 conductors		
<b>Conductor Size</b>	18 AWG		
<b>Conductor Stranding</b>	16-stranded		
<b>Conductor Material</b>	Bare copper		
<b>Conductor Insulation Material</b>	TPE		
<b>Conductor Insulation Color</b>	Black and white		

## Agency Approvals

<b>UL Listed File #</b>	E46194
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	90458
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>