

SKH-M1TB-R Cut Sheet



Patlite SK series LED audible-visual signal beacon, 88 dB at 1m, intermittent tone(s), rotating (120rpm), red, 100mm, 12-24 VDC, IP23, push-in terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SKH-M1TB-R>

Technical Specifications

Brand	Patlite
Item	Audible-visual signal beacon
Series	SK
Bulb Type	LED
Operator Size	100mm
Operator Color	Red
Light Color(s)	Red
Light Function	Rotating (120rpm)
Housing Material	Polycarbonate
Material	Polycarbonate

Loudness Decibel	88 dB at 1m
Tone Frequency	2.5 kHz
Tone Type	Intermittent
Touch to Acknowledge	No
Voltage Rating	12-24 VDC
Mounting	Base
IP Rating	IP23
Connection	Push-in terminal
Additional Information	IP65 when used with SZW-103 rubber gasket

Agency Approvals

UL Listed File #	E215660
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SKH-M1TB-R.pdf>
See store item page for other formats.