

SKP-M2J-R Cut Sheet



Patlite SK series LED industrial signal beacon, 150mm, red, rotating (120rpm), IP23, base mount, 100-240 VAC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SKP-M2J-R>

Technical Specifications

| | |
|----------------|--------------------------|
| Brand | Patlite |
| Item | Industrial signal beacon |
| Bulb Type | LED |
| Series | SK |
| Operator Size | 150mm |
| Operator Color | Red |
| Light Color(s) | Red |

| | |
|----------------------|-------------------|
| Light Function | Rotating (120rpm) |
| Housing Material | Polycarbonate |
| Mounting | Base |
| IP Rating | IP23 |
| Connection | Pigtail |
| Touch to Acknowledge | No |
| Voltage Rating | 100-240 VAC |

Agency Approvals

| | |
|----------------------|----------------------------------------|
| UL Listed File # | E215660 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SKP-M2J-R.pdf>
See store item page for other formats.