

SL08-M2JN-R Cut Sheet



Patlite SL series LED industrial signal beacon, 80mm, red, selectable continuous, blinking or triple flash, IP23, base mount, 100-240 VAC. IP65 when used with SZW-102 rubber gasket.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SL08-M2JN-R>

Technical Specifications

Brand	Patlite
Item	Industrial signal beacon
Bulb Type	LED
Series	SL
Operator Size	80mm
Operator Color	Red
Light Color(s)	Red
Light Function	Selectable continuous, blinking or triple flash

Housing Material	Polycarbonate
Mounting	Base
IP Rating	IP23
Connection	Pigtail
Touch to Acknowledge	No
Voltage Rating	100-240 VAC
Additional Information	IP65 when used with SZW-102 rubber gasket

Agency Approvals

UL Listed File #	E215660
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SL08-M2JN-R.pdf>
See store item page for other formats.