

SL08-M2KTB-R Cut Sheet



Patlite SL series LED audible-visual signal beacon, 86 dB at 1m, continuous tone(s), selectable continuous, blinking or triple flash, red, 80mm, 100-240 VAC, IP66, NEMA 4X/13, push-in terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SL08-M2KTB-R>

Technical Specifications

| | |
|-------------------------|---|
| Brand | Patlite |
| Item | Audible-visual signal beacon |
| Series | SL |
| Bulb Type | LED |
| Operator Size | 80mm |
| Operator Color | Red |
| Light Color(s) | Red |
| Light Function | Selectable continuous, blinking or triple flash |
| Housing Material | Polycarbonate |
| Material | Polycarbonate |

| | |
|-----------------------------|------------------|
| Loudness Decibel | 86 dB at 1m |
| Tone Frequency | 2.5 kHz |
| Tone Type | Continuous |
| Touch to Acknowledge | No |
| Voltage Rating | 100-240 VAC |
| Mounting | Base |
| IP Rating | IP66 |
| NEMA Rating | 4X/13 |
| Connection | Push-in terminal |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E215660 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SL08-M2KTB-R.pdf>
See store item page for other formats.