

SL10-M2KTB-R Cut Sheet



Patlite SL series LED audible-visual signal beacon, 88 dB at 1m, continuous tone(s), selectable continuous, blinking or triple flash, red, 100mm, 100-240 VAC, IP66, NEMA 4X/13, push-in terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SL10-M2KTB-R>

Technical Specifications

Brand	Patlite
Item	Audible-visual signal beacon
Series	SL
Bulb Type	LED
Operator Size	100mm
Operator Color	Red
Light Color(s)	Red
Light Function	Selectable continuous, blinking or triple flash
Housing Material	Polycarbonate
Material	Polycarbonate

Loudness Decibel	88 dB at 1m
Tone Frequency	2.5 kHz
Tone Type	Continuous
Touch to Acknowledge	No
Voltage Rating	100-240 VAC
Mounting	Base
IP Rating	IP66
NEMA Rating	4X/13
Connection	Push-in terminal

Agency Approvals

UL Listed File #	E215660
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SL10-M2KTB-R.pdf>
See store item page for other formats.