

# SL4824-LR Cut Sheet



SOLO standard temperature controller, 1/32 DIN, 2-line LED, current, voltage, RTD or thermocouple input, 0-10 VDC, 3A SPST relay output, 100-240 VAC operating voltage, RS-485.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SL4824-LR>

## Technical Specifications

Brand	SOLO	Input RTD Signal Types	Pt100 and JPt100
Item	Standard temperature controller	Output	0-10 VDC, 3A SPST relay
Mounting	Panel	Operating Voltage	100-240 VAC
Mounting Hole Size	1/32 DIN	Control Mode	PID, ON/OFF, ramp/soak or manual
Display	2-line LED	Control Function	Single loop, heat only, cool only or heat/cool
Input Current Signal Range	Input current signal range(s) of 0-20 mA, 4-20 mA	Communication	RS-485
Input Voltage Signal Range	Input voltage signal range(s) of 0-5 VDC, 0-10 VDC, 0-50 mVDC		
Input Thermocouple Signal Type	J, K, T, N, E, R, S, B, L, U, TXK		

## Agency Approvals

UL Listed File #	E311366
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>