

SL4848-VR Cut Sheet



SOLO standard temperature controller, 1/16 DIN, 2-line LED, current, voltage, RTD or thermocouple input, 11-15 VDC pulse, 5A SPST relay, (2) 3A SPST relays output, 100-240 VAC operating voltage, RS-485.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SL4848-VR>

Technical Specifications

Brand	SOLO
Item	Standard temperature controller
Mounting	Panel
Mounting Hole Size	1/16 DIN
Display	2-line LED
Input Current Signal Range	0-20 mA, 4-20 mA
Input Voltage Signal Range	0-5 VDC, 0-10 VDC, 0-50 mVDC
Input Thermocouple Signal Type	J, K, T, N, E, R, S, B, L, U, TXK
Input RTD Signal Types	Pt100 and JPt100
Output	11-15 VDC pulse, 5A SPST relay, (2) 3A SPST relays
Operating Voltage	100-240 VAC
Control Mode	PID, ON/OFF, ramp/soak or manual
Control Function	Single loop, heat only, cool only or heat/cool
Communication	RS-485

Agency Approvals

UL Listed File #	E311366
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document