

SLA-10-100 Cut Sheet



Electri-Flex Liquatite liquid-tight flexible metallic conduit, hot dipped galvanized steel, PVC jacket, copper braided shield, 3/8in trade size, black, UL-360 Listed, 100ft/30.4m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SLA-10-100>

Technical Specifications

Brand	Electri-Flex	Color	Black
Series	Liquatite	Coil Length	100ft/30.4m
Item	Conduit	UL Rating	UL-360 Listed
Conduit Type	Liquid-tight flexible metallic conduit (LFMC)	Operating Temperature	-22 deg F to 176 deg F (-30 deg C to 80 deg C)
Liquid-tight	Yes	UV Resistant	Yes
Inner Core Material	Hot dipped galvanized steel	Applicable Standards	<ul style="list-style-type: none">• ANSI/UL-360• IEC 61386
Outer Material	PVC jacket	Application	EMI/RFI shielding
Shield Material	Copper braided		
Trade Size	3/8in		

Agency Approvals

UL Listed File #	E29278
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document