

# SLB4848-C0 Cut Sheet



SOLO basic temperature controller, 1/16 DIN, 2-line LCD, RTD or thermocouple input, 4-20 mA output, 100-240 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SLB4848-C0>

## Technical Specifications

<b>Brand</b>	SOLO
<b>Item</b>	Basic temperature controller
<b>Mounting</b>	Panel
<b>Mounting Hole Size</b>	1/16 DIN
<b>Display</b>	2-line LCD
<b>Input Thermocouple Signal Type</b>	J, K, T, N, E, R, S, B, L, U, TXK
<b>Input RTD Signal Types</b>	Pt100, JPt100, Cu50 and Ni120
<b>Output</b>	4-20 mA
<b>Operating Voltage</b>	100-240 VAC
<b>Control Mode</b>	PID, ON/OFF or manual
<b>Control Function</b>	Single loop, heat or cool

## Agency Approvals

<b>UL Listed File #</b>	E311366
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SLB4848-C0.pdf>  
See store item page for other formats.