

SLB4848-C2 Cut Sheet



SOLO basic temperature controller, 1/16 DIN, 2-line LCD, RTD or thermocouple input, 4-20mA, (2) 3A SPST relays output, 100-240 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SLB4848-C2>

Technical Specifications

Brand	SOLO
Item	Basic temperature controller
Mounting	Panel
Mounting Hole Size	1/16 DIN
Display	2-line LCD
Input Thermocouple Signal Type	J, K, T, N, E, R, S, B, L, U, TXK
Input RTD Signal Types	Pt100, JPt100, Cu50 and Ni120
Output	4-20mA, (2) 3A SPST relays
Operating Voltage	100-240 VAC
Control Mode	PID, ON/OFF or manual
Control Function	Single loop, heat only, cool only or heat/cool

Agency Approvals

UL Listed File #	E311366
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document