

SLB4848-V2 Cut Sheet



SOLO basic temperature controller, 1/16 DIN, 2-line LCD, RTD or thermocouple input, 12 VDC pulse, (2) 3A SPST relays output, 100-240 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SLB4848-V2>

Technical Specifications

Brand	SOLO
Item	Basic temperature controller
Mounting	Panel
Mounting Hole Size	1/16 DIN
Display	2-line LCD
Input Thermocouple Signal Type	J, K, T, N, E, R, S, B, L, U, TXK
Input RTD Signal Types	Pt100, JPt100, Cu50 and Ni120
Output	12 VDC pulse, (2) 3A SPST relays
Operating Voltage	100-240 VAC
Control Mode	PID, ON/OFF or manual
Control Function	Single loop, heat only, cool only or heat/cool

Agency Approvals

UL Listed File #	E311366
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SLB4848-V2.pdf>
See store item page for other formats.