

# SLS-R3-E Cut Sheet



Datalogic safety laser scanner, area protection, 275 degrees operating angle, 0.05–3m operating distance, 24 VDC, safety category Type 3, IP65, (2) 8-pin M12 quick-disconnects.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SLS-R3-E>

## Technical Specifications

<b>Brand</b>	Datalogic
<b>Item</b>	Safety laser scanner
<b>Series</b>	Sentinel
<b>Scanner Type</b>	Enhanced remote
<b>Function</b>	Area protection
<b>Operating Angle</b>	275 degrees
<b>Angular Resolution</b>	0.1 degree
<b>Operating Distance</b>	0.05–3m

<b>Configurable</b>	Yes
<b>Input Voltage</b>	24 VDC
<b>Safety Category</b>	Type 3
<b>Scanner Features</b>	Warning zones, muting and restart capability
<b>IP Rating</b>	IP65
<b>Connection</b>	(2) 8-pin M12 quick-disconnects
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E528762
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SLS-R3-E.pdf>  
See store item page for other formats.