

# SLT1-050-L140 Cut Sheet



ProSense hydrostatic submersible level transmitter, 0 to 50 psig (115.3ft of water column) sensing range, 1/2in male NPT with shielded and vented 140ft cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SLT1-050-L140>

## Technical Specifications

Brand	ProSense
Item	Submersible level transmitter
Sensor Type	Hydrostatic
Sensing Range	0 to 50 psig (115.3ft of water column)
Output	4-20 mA
Operating Voltage	9-28 VDC
Electrical Connection	1/2in male NPT with shielded and vented 140ft cable
Jacket Material	Polyurethane (PUR)

## Agency Approvals

UL Listed File #	E197886
UL Recognized File #	None
UL Hazardous File #	E197886
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">FM Approval Document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SLT1-050-L140.pdf>  
See store item page for other formats.