

SLT2-030-L100 Cut Sheet



ProSense hydrostatic submersible level transmitter, 0 to 30 psig (69.2ft of water column) sensing range, 1/2in male NPT with shielded and vented 100ft cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SLT2-030-L100>

Technical Specifications

| | |
|-----------------------|---|
| Brand | ProSense |
| Item | Submersible level transmitter |
| Sensor Type | Hydrostatic |
| Sensing Range | 0 to 30 psig (69.2ft of water column) |
| Output | 4-20 mA |
| Operating Voltage | 9-28 VDC |
| Electrical Connection | 1/2in male NPT with shielded and vented 100ft cable |
| Jacket Material | Polyurethane (PUR) |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E197886 |
| UL Recognized File # | None |
| UL Hazardous File # | E197886 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | FM Approval Document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SLT2-030-L100.pdf>
See store item page for other formats.