

SMC3DA4015DOL Cut Sheet



Eltwin SMC3-DOL series solid state contactor, 15A, (2) N.O. SCR switched, (1) Direct power poles, 400-480 VAC (50/60Hz) operating voltage, 24-60 VDC/24-480 VAC coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SMC3DA4015DOL>

Technical Specifications

Brand	Eltwin
Item	Contactor
Series	SMC3-DOL
Contactor Type	Solid state
Actuator Type	Electronic
Reversing	No
Amperage Rating	15A
Power Poles	(2) N.O. SCR switched, (1) Direct
Switching Type	Zero cross

Operating Voltage	400-480 VAC (50/60Hz)
Coil Voltage	24-60 VDC/24-480 VAC
Horsepower Rating	10hp
SCCR Rating	5kA SCCR
UL Rating	UL 508 rated
Protection Type(s)	Varistor surge protection
Mounting	35mm DIN rail or panel
Indicating Type	(1) status LED
Additional Information	Purchase overload protection switch separately

Agency Approvals

UL Listed File #	E207530
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SMC3DA4015DOL.pdf>
See store item page for other formats.