

SOHM-70C-19.05 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 70, 3/4in bore. Requires SOH-70-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOHM-70C-19.05>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	60 N-m
Maximum Torque	120 N-m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	3.5mm
Maximum RPM	4500
Attachment Style	Clamp
Coupling Size	70
Bore Diameter	3/4in
Outside Diameter	73mm
Clamp Screw Fastening Torque	30 N-m
Clamp Screw Size	M8
Requires	SOH-70-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement