

SOHM-70C-40 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 70, 40mm bore. Requires SOH-70-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOHM-70C-40>

Technical Specifications

| | |
|--------------------------------------|--------------------|
| Brand | Sung-II Machinery |
| Item | Drive coupling hub |
| Coupling Type | Oldham |
| Material | Aluminum alloy |
| Rated Torque | 65 N·m |
| Maximum Torque | 130 N·m |
| Maximum Angular Misalignment | 1.5 degrees |
| Maximum Parallel Misalignment | 3.5mm |
| Maximum RPM | 4500 |

| | |
|-------------------------------------|-------------------------|
| Attachment Style | Clamp |
| Coupling Size | 70 |
| Overall Length | 75.5mm |
| Bore Diameter | 40mm |
| Outside Diameter | 73mm |
| Clamp Screw Fastening Torque | 30 N·m |
| Clamp Screw Size | M8-1.25 x 30mm |
| Requires | SOH-70-DISC torque disc |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SOHM-70C-40.pdf>
See store item page for other formats.