

SOOW-10-2BK-1 Cut Sheet



Southwire portable cord, unshielded, SOOW, 600V, 2 conductors, 10 AWG, EPDM thermoset rubber conductor insulation material, black and white, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOOW-10-2BK-1>

Technical Specifications

Brand	Southwire
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SOOW
Applicable Standards	UL 62
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V
Conductors	2 conductors
Conductor Size	10 AWG
Conductor Stranding	104-stranded
Conductor Material	Bare copper
Conductor Insulation Material	EPDM thermoset rubber
Conductor Insulation Color	Black and white

Shielding	Unshielded
Jacket Material	CPE thermoset rubber
Jacket Color	Black
Nominal Overall Cable Diameter	0.62in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 100ft = 14 x 7in Reel, 101 to 140ft = 14 x 10in Reel, 141 to 220ft = 16 x 10in Reel, 221 to 310ft = 18 x 10in Reel, 311 to 410ft = 18 x 13in Reel, 411 to 880ft = 24 x 17in Wooden Reel, 881 to 1450ft = 30 x 17in Wooden Reel, 1451 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement