

SOOW-14-2BK-1 Cut Sheet



Southwire portable cord, unshielded, SOOW, 600V, 2 conductors, 14 AWG, EPDM thermoset rubber conductor insulation material, black and white, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOOW-14-2BK-1>

Technical Specifications

| | |
|--------------------------------------|-----------------------|
| Brand | Southwire |
| Item | Cord |
| Wire/Cable Type | Portable |
| UL Wire/Cable Type | SOOW |
| Applicable Standards | UL 62 |
| Application | General purpose |
| Flexibility | Flexible |
| Voltage Rating | 600V |
| Conductors | 2 conductors |
| Conductor Size | 14 AWG |
| Conductor Stranding | 41-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | EPDM thermoset rubber |
| Conductor Insulation Color | Black and white |

| | |
|---------------------------------------|---|
| Shielding | Unshielded |
| Jacket Material | CPE thermoset rubber |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 0.5in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 20 to 50ft = Coil• 51 to 155ft = 14 x 7in Reel• 156 to 225ft = 14 x 10in Reel• 226 to 340ft = 16 x 10in Reel• 341 to 475ft = 18 x 10in Reel• 476 to 620ft = 18 x 13in Reel• 621 to 1390ft = 24 x 17in Wooden Reel• 1391 to 2220ft = 30 x 17in Wooden Reel• 2221 to 5000ft = Large Wooden Reel |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E46194 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 90458 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |