

SOOW-14-2BK-1 Cut Sheet



Southwire portable cord, unshielded, SOOW, 600V, 2 conductors, 14 AWG, EPDM thermoset rubber conductor insulation material, black and white, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOOW-14-2BK-1>

Technical Specifications

Brand	Southwire	Shielding	Unshielded
Item	Cord	Jacket Material	CPE thermoset rubber
Wire/Cable Type	Portable	Jacket Color	Black
UL Wire/Cable Type	SOOW	Nominal Overall Cable Diameter	0.5in
Applicable Standards	UL 62	Bulk Length	Cut to length
Application	General purpose	Package Type	1 to 50ft = Coil, 51 to 150ft = 14 x 7in Reel, 151 to 220ft = 14 x 10in Reel, 221 to 340ft = 16 x 10in Reel, 341 to 480ft = 18 x 10in Reel, 481 to 630ft = 18 x 13in Reel, 631 to 1360ft = 24 x 17in Wooden Reel, 1361 to 2240ft = 30 x 17in Wooden Reel, 2241 to MAX = Large Wooden Reel
Flexibility	Flexible		
Voltage Rating	600V		
Conductors	2 conductors		
Conductor Size	14 AWG		
Conductor Stranding	41-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	EPDM thermoset rubber		
Conductor Insulation Color	Black and white		

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement