

SOOW-16-3BK-1 Cut Sheet



Southwire portable cord, unshielded, SOOW, 600V, 3 conductors (includes ground), 16 AWG, EPDM thermoset rubber conductor insulation material, black, white and green, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOOW-16-3BK-1>

Technical Specifications

Brand	Southwire
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SOOW
Applicable Standards	UL 62
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V
Conductors	3 conductors (includes ground)
Conductor Size	16 AWG
Conductor Stranding	26-stranded
Conductor Material	Bare copper
Conductor Insulation Material	EPDM thermoset rubber
Conductor Insulation Color	Black, white and green

Shielding	Unshielded
Jacket Material	CPE thermoset rubber
Jacket Color	Black
Nominal Overall Cable Diameter	0.39in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 250ft = 14 x 7in Reel, 251 to 360ft = 14 x 10in Reel, 361 to 560ft = 16 x 10in Reel, 561 to 800ft = 18 x 10in Reel, 801 to 1040ft = 18 x 13in Reel, 1041 to 2240ft = 24 x 17in Wooden Reel, 2241 to 3680ft = 30 x 17in Wooden Reel, 3681 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement