

SOOW-18-3BK-1 Cut Sheet



Southwire portable cord, unshielded, SOOW, 600V, 3 conductors (includes ground), 18 AWG, EPDM thermoset rubber conductor insulation material, black, white and green, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOOW-18-3BK-1>

Technical Specifications

Brand	Southwire
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SOOW
Applicable Standards	UL 62
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V
Conductors	3 conductors (includes ground)
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Bare copper
Conductor Insulation Material	EPDM thermoset rubber

Conductor Insulation Color	Black, white and green
Shielding	Unshielded
Jacket Material	CPE thermoset rubber
Jacket Color	Black
Nominal Overall Cable Diameter	0.365in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 1 to 75ft = Coil• 76 to 290ft = 14 x 7in Reel• 291 to 420ft = 14 x 10in Reel• 421 to 650ft = 16 x 10in Reel• 651 to 910ft = 18 x 10in Reel• 911 to 1190ft = 18 x 13in Reel• 1191 to 2550ft = 24 x 17in Wooden Reel• 2551 to 4200ft = 30 x 17in Wooden Reel• 4201 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement