

# SOOW-6-3BK-1 Cut Sheet



Direct Wire portable cord, unshielded, SOOW, 600V, 3 conductors (includes ground), 6 AWG, EPDM thermoset rubber conductor insulation material, black, white and green, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOOW-6-3BK-1>

## Technical Specifications

<b>Brand</b>	Direct Wire
<b>Item</b>	Cord
<b>Wire/Cable Type</b>	Portable
<b>UL Wire/Cable Type</b>	SOOW
<b>Application</b>	Power
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	600V
<b>Conductors</b>	3 conductors (includes ground)
<b>Conductor Size</b>	6 AWG
<b>Conductor Stranding</b>	260-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	EPDM thermoset rubber
<b>Conductor Insulation Color</b>	Black, white and green

<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	CPE thermoset rubber
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.761in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 10 to 30ft = Coil</li><li>• 31 to 65ft = 14 x 7in Reel</li><li>• 66 to 95ft = 14 x 10in Reel</li><li>• 96 to 145ft = 16 x 10in Reel</li><li>• 146 to 205ft = 18 x 10in Reel</li><li>• 206 to 270ft = 18 x 13in Reel</li><li>• 271 to 600ft = 24 x 17in Wooden Reel</li><li>• 601 to 960ft = 30 x 17in Wooden Reel</li><li>• 961 to 2500ft = Large Wooden Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	none
<b>UL Recognized File #</b>	none
<b>UL Hazardous File #</b>	none
<b>CSA File #</b>	none
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>