

SP350MQMJ Cut Sheet



Hammond control transformer, open core, 350 VA, 1-phase, 240/480 VAC primary, 120/240 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SP350MQMJ>

Technical Specifications

Brand	Hammond
Series	Spartan
Item	Transformer
Transformer Type	Control
Core Type	Open
Power Rating	350 VA
Number of Phases	1
Primary Voltage	240/480 VAC
Secondary Voltage	120/240 VAC
Frequency	50/60 Hz
Electrostatic Shield	No
Mounting	Panel

Agency Approvals

UL Listed File #	E50394
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR 3902
RoHS Status	No
EU REACH	View EU REACH document