

SPC125U Cut Sheet

Bryant standard duty support grip, accepts cable diameter size 1.25 to 1.49in, closed, tin-coated bronze mesh, 15in length, single, eye length 10in, indoor and outdoor applications.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SPC125U>



Technical Specifications

Brand	Bryant
Item	Cord grip
Grip Type	Support
Application	Standard duty
Low Tension	No
Cable Diameter Size	1.25 to 1.49in
Mesh Type	Closed
Mesh Material	Tin-coated bronze
Mesh Length	15in
Eye Type	Single
Eye Length	10in
Environmental Requirements	Indoor and outdoor applications

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	701228
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SPC125U.pdf>
See store item page for other formats.