

# SPT25-10-0100D Cut Sheet



ProSense pressure transmitter, 0 to 100 psig range, +/- 0.5% accuracy, stainless steel sensing element, 0-10 VDC analog output, 1/4in male NPT process connection, 14-36 VDC operating voltage, DIN 175301-803C L-connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SPT25-10-0100D>

## Technical Specifications

Brand	ProSense
Item	Pressure transmitter
Pressure Range	0 to 100 psig
Accuracy	+/- 0.5% of full range
Sensing Element Material	Stainless steel
Analog Output	0-10 VDC
Process Connection	1/4in male NPT
Operating Voltage	14-36 VDC
Electrical Connection	DIN 175301-803C L-connector
Media Type	Liquid and gases

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SPT25-10-0100D.pdf>  
See store item page for other formats.