

SPT25-10-3000D Cut Sheet



ProSense pressure transmitter, 0 to 3000 psig range, +/- 0.5% accuracy, stainless steel sensing element, 0-10 VDC analog output, 1/4in male NPT process connection, 14-36 VDC operating voltage, DIN 175301-803C L-connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SPT25-10-3000D>

Technical Specifications

| | |
|--------------------------|-----------------------------|
| Brand | ProSense |
| Item | Pressure transmitter |
| Pressure Range | 0 to 3000 psig |
| Accuracy | +/- 0.5% of full range |
| Sensing Element Material | Stainless steel |
| Analog Output | 0-10 VDC |
| Process Connection | 1/4in male NPT |
| Operating Voltage | 14-36 VDC |
| Electrical Connection | DIN 175301-803C L-connector |
| Media Type | Liquid and gases |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SPT25-10-3000D.pdf>
See store item page for other formats.