

SPT25-10-V30A Cut Sheet



ProSense pressure transmitter, -14.7 to 30 psig range, +/- 0.5% accuracy, stainless steel sensing element, 0-10 VDC analog output, 1/4in male NPT process connection, 14-36 VDC operating voltage, 6.6ft/2m cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SPT25-10-V30A>

Technical Specifications

Brand	ProSense
Item	Pressure transmitter
Pressure Range	-14.7 to 30 psig
Accuracy	+/- 0.5% of full range
Sensing Element Material	Stainless steel
Analog Output	0-10 VDC
Process Connection	1/4in male NPT
Operating Voltage	14-36 VDC
Electrical Connection	6.6ft/2m cable
Media Type	Liquid and gases

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SPT25-10-V30A.pdf>
See store item page for other formats.