

SPT25-20-1500A Cut Sheet



ProSense pressure transmitter, 0 to 1500 psig range, +/-0.5% accuracy, stainless steel sensing element, 4-20 mA analog output, 1/4in male NPT process connection, 9 to 36 VDC operating voltage, 6.6ft cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SPT25-20-1500A>

Technical Specifications

Brand	ProSense
Item	Pressure transmitter
Pressure Range	0 to 1500 psig
Accuracy	+/-0.5% of full range
Sensing Element Material	Stainless steel
Analog Output	4-20 mA
Process Connection	1/4in male NPT
Operating Voltage	9 to 36 VDC
Electrical Connection	6.6ft cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document