

SPTD25-20-0200H Cut Sheet



ProSense pressure transmitter, 0 to 200 psig range, +/-0.5% accuracy, stainless steel sensing element, 4-20 mA analog output, 1/4in male NPT process connection, 8.5 to 36 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SPTD25-20-0200H>

Technical Specifications

Brand	ProSense
Item	Pressure transmitter
Pressure Range	0 to 200 psig
Accuracy	+/-0.5% of full range
Sensing Element Material	Stainless steel
Analog Output	4-20 mA
Process Connection	1/4in male NPT
Operating Voltage	8.5 to 36 VDC
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document