

SR0921Q0601 Cut Sheet



CCEA SIRIO Q series LED work light, 100 x 100 x 25mm, 12-24 VDC operating voltage, daylight white, 5000K, 16W, 1450 lm, bracket mount, pigtail, aluminum body, 9.8ft/3m cable length, IP67 and IP69. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR0921Q0601>

Technical Specifications

Brand	CCEA
Item	LED work light
Series	SIRIO Q
Size	100 x 100 x 25mm
Operating Voltage	12-24 VDC
LED Color	Daylight white
Color Temperature	5000K
Luminous Flux	1450 lm

Mounting	Bracket
Connection	Pigtail
Power Consumption	16W
Body Material	Aluminum
Cable Length	9.8ft/3m
IP Rating	IP67 and IP69
Includes	Mounting bracket

Agency Approvals

UL Listed File #	None
UL Recognized File #	E506617
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SR0921Q0601.pdf>
See store item page for other formats.