

SR0924Q0201 Cut Sheet



CCEA SIRIO Q series LED work light, 100 x 100 x 25mm, 120 VAC operating voltage, daylight white, 5000K, 17W, 1200 lm, bracket mount, pigtail, aluminum body, 9.8ft/3m cable length, IP67 and IP69. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR0924Q0201>

Technical Specifications

Brand	CCEA
Item	LED work light
Series	SIRIO Q
Size	100 x 100 x 25mm
Operating Voltage	120 VAC
LED Color	Daylight white
Color Temperature	5000K
Luminous Flux	1200 lm
Mounting	Bracket
Connection	Pigtail
Power Consumption	17W
Body Material	Aluminum
Cable Length	9.8ft/3m
IP Rating	IP67 and IP69
Includes	Mounting bracket

Agency Approvals

UL Listed File #	None
UL Recognized File #	E526603
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document