

# SR22-12 Cut Sheet



Stellar SR22 series compact soft starter, 12A, 110-240 VAC at 1-phase/208-460 VAC at 3-phase, Trip Class 2/10/20/30, rated for 10 start/hour, internally bypassed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR22-12>

## Technical Specifications

Brand	Stellar
Item	Soft starter
Controller Type	Compact
Series	SR22
Amperage Rating	12A
Nominal Input Voltage	110-240 VAC at 1-phase/208-460 VAC at 3-phase
Nominal Output Voltage	110-240 VAC at 1-phase/208-460 VAC at 3-phase
Trip Class	Trip Class 2/10/20/30
Starts per Hour	10
Internally Bypassed	Yes
Number of Input Phases	1 and 3
Number of Output Phases	1 and 3
Number of Controlled Output Phases	2

Control Mode	Sinusoidal
Control Power Requirement	24 VDC
Derating	Unit may require derating for applications other than fans and pumps; see specifications for appropriate derating
Temperature Rating	0 to 40 deg C
Enclosure Type	Enclosed
Mounting	35mm DIN rail
Frame Size	45mm
IP Rating	IP20
Output Frequency Range	0-60 Hz
Output Type	SCR output
Reverse Capability	None

## Agency Approvals

UL Listed File #	E333109
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>