

# SR35-041 Cut Sheet



Stellar SR35 series basic soft starter, 41A, 110-240 VAC at 1-phase/208-460 VAC at 3-phase, Trip Class 10/20/30, rated for 5 start/hour, internally bypassed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR35-041>

## Technical Specifications

|  |   |
|--|---|
| <b>Brand</b>                                     | Stellar                                       |
| <b>Item</b>                                      | Soft starter                                  |
| <b>Controller Type</b>                           | Basic   |
| <b>Series</b>                                    | SR35  |
| <b>Amperage Rating</b>                           | 41A   |
| <b>Nominal Input Voltage</b>                     | 110-240 VAC at 1-phase/208-460 VAC at 3-phase |
| <b>Nominal Output Voltage</b>                    | 110-240 VAC at 1-phase/208-460 VAC at 3-phase |
| <b>Trip Class</b>                                | Trip Class 10/20/30                           |
| <b>Starts per Hour</b>                           | 5   |
| <b>Internally Bypassed</b>                       | Yes   |
| <b>Number of Input Phases</b>                    | 1 and 3                                       |
| <b>Number of Output Phases</b>                   | 1 and 3                                       |
| <b>Number of Controlled Output Phases</b>        | 2   |
| <b>Control Mode</b>                              | Sinusoidal                                    |
| <b>Control Power Requirement</b>                 | 24 VDC  |
| <b>Communication Port and Connection Type(s)</b> | (1) RS-485 (RJ12)                             |

|                               |   |
|-------------------------------|---|
| <b>Port Protocol(s)</b>       | Modbus RTU  |
| <b>Port Speed(s)</b>          | up to 115.2k baud   |
| <b>Derating</b>               | Unit may require derating for applications other than fans and pumps; see specifications for appropriate derating   |
| <b>Temperature Rating</b>     | -20 to 40 deg C   |
| <b>Enclosure Type</b>         | Enclosed  |
| <b>Mounting</b>               | Panel   |
| <b>Frame Size</b>             | 1   |
| <b>Output Frequency Range</b> | 50-60 Hz  |
| <b>Output Type</b>            | SCR output  |
| <b>Reverse Capability</b>     | None  |
| <b>Dangerous Goods</b>        | <ul style="list-style-type: none"><li>• Hazard Type: Lithium Battery</li><li>• Packing Instruction: 970</li><li>• UN Number: UN3091</li><li>• Battery Included: True</li><li>• Battery Installed: Yes</li><li>• Generic Battery Number: CR1632</li><li>• Battery Type: Button</li><li>• Lithium Content: 0.03600g</li></ul> |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E333109                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SR35-041.pdf>  
See store item page for other formats.