

SR35-AUX-IO Cut Sheet



Stellar SR35 series temperature combo module, thermistor, 1-channel input, 2-point input, 110-230 VAC/24 VDC, 2-point output, 250 VAC, (2) Form A (SPST) relays. For use with Stellar SR35 series soft starters. (1) 500mm ribbon cable included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR35-AUX-IO>

Technical Specifications

Brand	Stellar
Item	Combo module
I/O Module Type	Temperature
Input Signal Type(s)	Thermistor
Series	SR35
Number Of Input Channels	1
Input Thermistor Signal Types	4K (PTC)
Number of Input Points	2
Nominal Input Voltage	110-230 VAC/24 VDC
Discrete Input Type	Sinking

Number of Output Points	2
Nominal Output Voltage	250 VAC
Discrete Output Type	Relay
Relay Configuration	(2) Form A (SPST) relays
Load Current	0.75A/point
Number of Isolated Discrete Output Commons	2
Number of Points per Discrete Output Common	1
For Use With	Stellar SR35 series soft starters
Includes	(1) 500mm ribbon cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SR35-AUX-IO.pdf>
See store item page for other formats.