

SR44-485HD15-CBL-2 Cut Sheet



ZIPLink soft starter cable, 6-pin RJ45 to 15-pin D-sub HD15 male, shielded, twisted pair, RS-485, 6.5ft/2m cable length. For use with Stellar soft starters.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR44-485HD15-CBL-2>

Technical Specifications

Brand	ZIPLink
Item	Cable
Cable Type	Soft starter
Device Connection	6-pin RJ45
ZIPLink Connection	15-pin D-sub HD15 male
Shielded	Yes
Twisted Pair	Yes
Serial Interface	RS-485
Cable Length	6.5ft/2m
Conductor Size	26 AWG
For Use With	Stellar soft starters

Agency Approvals

UL Listed File #	None
UL Recognized File #	157382
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document