

SR55-302 Cut Sheet



Stellar SR55 series full-featured soft starter, 302A, 200-480 VAC at 3-phase, Trip Class 10/20/30, rated for 3 start/hour, internally bypassed, 3 frame. Optional EtherNet/IP and Modbus TCP cards available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR55-302>

Technical Specifications

Brand	Stellar
Item	Soft starter
Controller Type	Full-featured
Series	SR55
Amperage Rating	302A
Nominal Input Voltage	208 VAC/220-240 VAC/440-480 VAC
Nominal Output Voltage	208 VAC/220-240 VAC/440-480 VAC
Trip Class	Trip Class 10/20/30
Starts per Hour	3
Internally Bypassed	Yes
Number of Input Phases	3
Number of Output Phases	3
Number of Controlled Output Phases	3
Control Mode	Sinusoidal
Control Power Requirement	24 VDC and 110 VAC or 230 VAC
Communication Port and Connection Type(s)	(1) RS-485 (RJ12)
Port Protocol(s)	Modbus RTU
Port Speed(s)	up to 115.2k baud

Derating	Unit may require derating for applications other than fans and pumps; see specifications for appropriate derating
Temperature Rating	-20 to 50 deg C
Enclosure Type	Open
Mounting	Panel
Frame Size	3
IP Rating	IP00
Output Frequency Range	0-60 Hz
Output Type	SCR output
Reverse Capability	None
SCCR Rating	18kA SCCR
Additional Information	Optional EtherNet/IP and Modbus TCP cards available
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.04• Replacement Battery: BR1632• Generic Battery: BR1632

Agency Approvals

UL Listed File #	ETL
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	ETL
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	Link to ETL Website

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SR55-302.pdf>
See store item page for other formats.