

SR55-CM-ENETIP2 Cut Sheet



Stellar SR55 series communication module, EtherNet/IP, 2 ports, (2) Ethernet (RJ45 full duplex) port(s). For use with Stellar SR55 series soft starters.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR55-CM-ENETIP2>

Technical Specifications

| | |
|--|---|
| Brand | Stellar |
| Item | Communication module |
| Series | SR55 |
| Number of Ports | 2 |
| Communication Port and Connection Type(s) | (2) Ethernet (RJ45 full duplex) |
| Port Protocol(s) | <ul style="list-style-type: none">• EtherNet/IP adapter• EtherNet/IP implicit messaging• EtherNet/IP explicit messaging• TCP/IP• CIP• transformer isolated interface |
| Port Speed(s) | 10/100 Mbps |
| For Use With | Stellar SR55 series soft starters |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |