

# SR55-CM-ENETIP Cut Sheet



Stellar SR55 series communication module, EtherNet/IP, 2 ports, (2) Ethernet (RJ45 full duplex) port(s). For use with Stellar SR55 series soft starters.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR55-CM-ENETIP>

## Technical Specifications

Brand	Stellar
Item	Communication module
Series	SR55
Number of Ports	2
Communication Port and Connection Type(s)	(2) Ethernet (RJ45 full duplex)
Port Protocol(s)	<ul style="list-style-type: none"><li>• EtherNet/IP adapter</li><li>• EtherNet/IP implicit messaging</li><li>• EtherNet/IP explicit messaging</li><li>• TCP/IP</li><li>• CIP</li><li>• transformer isolated interface</li></ul>
Port Speed(s)	10/100 Mbps
For Use With	Stellar SR55 series soft starters

## Agency Approvals

UL Listed File #	E214107
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>